

Molle forate per stampi			Ultraflex 82 Shore A			Ultraflex 92 Shore A			Ultraflex 94 Shore A			Adipol 90 Shore A			
Compressione massima			35%			30%			25%			30%			
Codice	A mm	B mm	H mm	S mm	D mm	Kp N	S mm	D mm	Kp N	S mm	D mm	Kp N	S mm	D mm	Kp N
MF-16x16	16	6,5	16	5,6	22	800	4,8	19	1300	4	19	1600	4,8	20	1400
MF-16x20			20	7			6			5			6		
MF-16x25			25	8,7			7,5			6,2			7,5		
MF-16x32			32	11,2			9,6			8			9,6		
MF-20x16	20	8,5	16	5,6	28	1500	4,8	26	2000	4	25	3250	4,8	27	2100
MF-20x20			20	7			6			5			6		
MF-20x25			25	8,7			7,5			6,2			7,5		
MF-20x32			32	11,2			9,6			8			9,6		
MF-20x40	40	14	12	10	12	2100									
MF-25x16	25	10,5	16	5,6	33	2100	4,8	30	3000	4	29	4500	4,8	31	3100
MF-25x20			20	7			6			5			6		
MF-25x25			25	8,7			7,5			6,2			7,5		
MF-25x32			32	11,2			9,6			8			9,6		
MF-25x40			40	14			12			10			12		
MF-25x50			50	17,5			15			12,5			15		
MF-32x16	32	13,5	16	5,6	43	3600	4,8	41	5800	4	38	8000	4,8	40	5800
MF-32x20			20	7			6			5			6		
MF-32x25			25	8,7			7,5			6,2			7,5		
MF-32x32			32	11,2			9,6			8			9,6		
MF-32x40			40	14			12			10			12		
MF-32x50			50	17,5			15			12,5			15		
MF-32x63	63	22	19	15,7	19	5800									
MF-40x20	40	13,5	20	7	54	6500	6	50	12000	5	47	15000	6	50	9000
MF-40x25			25	8,7			7,5			6,2			7,5		
MF-40x32			32	11,2			9,6			8			9,6		
MF-40x40			40	14			12			10			12		
MF-40x50			50	17,5			15			12,5			15		
MF-40x63			63	22			19			15,7			19		
MF-40x80	80	28	24	20	24	9000									
MF-50x25	50	17	25	8,7	65	11000	7,5	62	17000	6,2	60	20000	7,5	62	16000
MF-50x32			32	11,2			9,6			8			9,6		
MF-50x40			40	14			12			10			12		
MF-50x50			50	17,5			15			12,5			15		
MF-50x63			63	22			19			15,7			19		
MF-50x80			80	28			24			20			24		
MF-50x100			100	35			30			25			30		
MF-63x32	63	17	32	11,2	81	16000	9,6	78	25000	8	74	35000	9,6	76	25000
MF-63x40			40	14			12			10			12		
MF-63x50			50	17,5			15			12,5			15		
MF-63x63			63	22			19			15,7			19		
MF-63x80			80	28			24			20			24		
MF-63x100			100	35			30			25			30		
MF-63x125	125	43,7	37,5	31,2	37,5	25000									
MF-80x40	80	21	40	14	103	26000	12	98	43000	10	95	60000	12	98	40000
MF-80x50			50	17,5			15			12,5			15		
MF-80x63			63	22			19			15,7			19		
MF-80x80			80	28			24			20			24		
MF-80x100			100	35			30			25			30		
MF-80x125			125	43,7			37,5			31,2			37,5		
MF-80x160	160	56	48	40	48	40000									
MF-100x50	100	21	50	17,5	126	43000	15	120	65000	12,5	120	100000	15	123	56000
MF-100x63			63	22			19			15,7			19		
MF-100x80			80	28			24			20			24		
MF-100x100			100	35			30			25			30		
MF-100x125			125	43,7			37,5			31,2			37,5		
MF-100x160			160	56			48			40			48		
MF-125x63	125	27	63	22	160	64000	19	152	105000	15,7	150	150000	19	155	90000
MF-125x80			80	28			24			20			24		
MF-125x100			100	35			30			25			30		
MF-125x125			125	43,7			37,5			31,2			37,5		
MF-125x160			160	56			48			40			48		
MF-125x200			200	70			60			50			60		