

Polycarbonate enclosures PK



PK accessories Page 27 System accessories Page 507 Cable gland, polyamide Page 658

Material:

- Housing: Fibre-glass reinforced polycarbonate
- Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal
- Cover transparent: Polycarbonate, all-round foamed-in PU seal
- Cover screws: Polyamide
- Insulating bungs: Polyethylene

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 66

Supply includes:

- Enclosure with cover
- Cover screws
- Insulating bungs for wall mounting screws

Approvals:

- UL
- cUL

Technical details:

Available on the Internet

without knockouts

| Width mm | | 65 | 94 | 94 | 94 | 110 | 110 | Page |
|------------------|------|--------------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Height mm | | 65 | 65 | 94 | 94 | 110 | 110 | |
| Depth mm | | 57 | 57 | 57 | 81 | 66 | 90 | |
| Model No. | | 9500.000 | 9502.000 | 9504.000 | 9505.000 | 9506.000 | 9507.000 | |
| Cover | Grey | Packs of 12 pc(s). | 8 pc(s). | 6 pc(s). | 6 pc(s). | 6 pc(s). | 6 pc(s). | |

Accessories

| | | | | | | | | |
|------------------------|-----------|----------|----------|----------|----------|----------|----------|----|
| Mounting plate | | - | - | - | - | - | - | |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | | - | - | - | - | - | - | |

without knockouts

| Width mm | | 130 | 130 | 130 | 130 | 180 | 180 | Page |
|------------------|------|-------------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Height mm | | 94 | 94 | 130 | 130 | 94 | 94 | |
| Depth mm | | 57 | 81 | 75 | 99 | 57 | 81 | |
| Model No. | | 9508.000 | 9509.000 | 9510.000 | 9511.000 | 9512.000 | 9513.000 | |
| Cover | Grey | Packs of 4 pc(s). | 4 pc(s). | 4 pc(s). | 4 pc(s). | 2 pc(s). | 2 pc(s). | |

Accessories

| | | | | | | | | |
|------------------------|-----------|----------|----------|----------|----------|----------|----------|----|
| Mounting plate | | - | - | - | - | - | - | |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | | - | - | - | - | - | - | |

Polycarbonate enclosures PK

without knockouts

| | | | | | | | | |
|------------------------|-------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Width mm | Packs of | 180 | 180 | 180 | 180 | 180 | 180 | Page |
| Height mm | | 110 | 110 | 110 | 110 | 110 | 110 | |
| Depth mm | | 90 | 90 | 111 | 111 | 165 | 165 | |
| Model No. | 2 pc(s). | 9514.000 | 9514.100 | 9515.000 | 9515.100 | 9516.000 | 9516.100 | |
| Cover | Grey | ■ | – | ■ | – | ■ | – | |
| | Transparent | – | ■ | – | ■ | – | ■ | |
| Accessories | | | | | | | | |
| Mounting plate | | – | – | – | – | – | – | |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | 10 set(s) | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 27 |

without knockouts

| | | | | | | | | |
|------------------------|-------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Width mm | Packs of | 182 | 182 | 182 | 182 | 182 | 182 | Page |
| Height mm | | 180 | 180 | 180 | 180 | 180 | 180 | |
| Depth mm | | 90 | 90 | 111 | 111 | 165 | 165 | |
| Model No. | 1 pc(s). | 9517.000 | 9517.100 | 9518.000 | 9518.100 | 9519.000 | 9519.100 | |
| Cover | Grey | ■ | – | ■ | – | ■ | – | |
| | Transparent | – | ■ | – | ■ | – | ■ | |
| Accessories | | | | | | | | |
| Mounting plate | 10 pc(s). | 9548.000 | 9548.000 | 9548.000 | 9548.000 | 9548.000 | 9548.000 | 27 |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | 10 set(s) | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 27 |

without knockouts

| | | | | | | | | |
|------------------------|-------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Width mm | Packs of | 254 | 254 | 254 | 254 | 254 | 254 | Page |
| Height mm | | 180 | 180 | 180 | 180 | 180 | 180 | |
| Depth mm | | 90 | 90 | 111 | 111 | 165 | 165 | |
| Model No. | 1 pc(s). | 9520.000 | 9520.100 | 9521.000 | 9521.100 | 9522.000 | 9522.100 | |
| Cover | Grey | ■ | – | ■ | – | ■ | – | |
| | Transparent | – | ■ | – | ■ | – | ■ | |
| Accessories | | | | | | | | |
| Mounting plate | 8 pc(s). | 9549.000 | 9549.000 | 9549.000 | 9549.000 | 9549.000 | 9549.000 | 27 |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | 10 set(s) | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 27 |

without knockouts

| | | | | | | | | |
|------------------------|-------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|------|
| Width mm | Packs of | 360 | 360 | 360 | 360 | 360 | 360 | Page |
| Height mm | | 254 | 254 | 254 | 254 | 254 | 254 | |
| Depth mm | | 111 | 111 | 165 | 165 | 165 | 165 | |
| Model No. | 1 pc(s). | 9523.000 | 9523.100 | 9524.000 | 9524.100 | 9524.100 | 9524.100 | |
| Cover | Grey | ■ | – | ■ | – | – | – | |
| | Transparent | – | ■ | – | – | ■ | ■ | |
| Accessories | | | | | | | | |
| Mounting plate | 4 pc(s). | 9550.000 | 9550.000 | 9550.000 | 9550.000 | 9550.000 | 9550.000 | 27 |
| Wall mounting brackets | 1 pack(s) | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 9583.000 | 27 |
| Hinges | 10 set(s) | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 9581.000 | 27 |