


SERIES 72



SILICONE RUBBER WHEELS FOR HIGH TEMPERATURES ALUMINIUM CENTRE FIXED BRACKET TYPE "NL"

Wheel description




Tread: Red non-staining silicone rubber wheels, hardness 80+/-5 Shore A; resistant to temperatures from -30°C and +250°C.

Centre: aluminium with threadguards.

Hub: The housing is obtained by moulding and turning and contains ball bearings series Z.

Bracket description

Standard duty bracket type NL (max. carrying capacity 400 daN)



The bracket is made by an electrolytically galvanised steel fork