


## Adjustable stud barrel tees

With taper and O-ring  
Cutting ring connection  
at tube end

Thread:  
Whitworth pipe thread,  
straight

Sealed with PEFLEX seal



Series Tube OD d1	Pressure	d2		SW1	SW2	SW3	l1* approx.	l2	l3	l5	i	kg/100 approx.	Order No. Single component	Order No. **
L 6	PN 500	G 1/8 A		14	12	14	27	12	34.5	26	8	6.1	1 1 63 01 20 00***	1 1 63 00 20 XX
L 8	PN 500	G 1/4 A		19	14	17	29	14	37.5	27.5	12	9.8	1 1 63 06 20 00	1 1 63 05 20 XX
L 10	PN 500	G 1/4 A		19	17	19	30	15	40	29	12	12.4	1 1 63 11 20 00	1 1 63 10 20 XX
L 12	PN 400	G 3/8 A		22	19	22	32	17	42	29.5	12	16.5	1 1 63 16 20 00	1 1 63 15 20 XX
L 15	PN 400	G 1/2 A		27	19	27	36	21	46.5	32.5	14	22.7	1 1 63 21 20 00	1 1 63 20 20 XX
L 18	PN 400	G 1/2 A		27	24	32	40	23.5	50	35.5	14	27.8	1 1 63 26 20 00	1 1 63 25 20 XX
L 22	PN 250	G 3/4 A		32	27	36	44	27.5	55	38.5	16	38.0	1 1 63 31 20 00	1 1 63 30 20 XX
L 28	PN 250	G 1 A		41	36	41	47	30.5	59	41.5	18	56.4	1 1 63 36 20 00	1 1 63 35 20 XX
L 35	PN 250	G 1 1/4 A		50	41	50	56	34.5	68.5	51	20	68.4	1 1 63 41 20 00	1 1 63 40 20 XX
L 42	PN 250	G 1 1/2 A		55	50	60	63	40	75	56	22	140.0	1 1 63 46 20 00	1 1 63 45 20 XX
S 6	PN 800	G 1/4 A		19	14	17	31	16	40	27	12	7.9	1 1 63 51 20 00	1 1 63 50 20 XX
S 8	PN 800	G 1/4 A		19	17	19	32	17	42.5	27.5	12	14.5	1 1 63 56 20 00	1 1 63 55 20 XX
S 10	PN 800	G 3/8 A		22	19	22	34	17.5	45	30	12	17.8	1 1 63 61 20 00	1 1 63 60 20 XX
S 12	PN 630	G 3/8 A		22	17	24	38	21.5	48	31	12	19.6	1 1 63 66 20 00	1 1 63 65 20 XX
S 14	PN 630	G 1/2 A		27	19	27	40	22	54	35	14	17.9	1 1 63 71 20 00	1 1 63 70 20 XX
S 16	PN 630	G 1/2 A		27	24	30	43	24.5	55	36.5	14	31.8	1 1 63 76 20 00	1 1 63 75 20 XX
S 20	PN 420	G 3/4 A		32	27	36	48	26.5	65	44.5	16	35.9	1 1 63 81 20 00	1 1 63 80 20 XX
S 25	PN 420	G 1 A		41	36	46	54	30	73	50	18	63.8	1 1 63 86 20 00	1 1 63 85 20 XX
S 30	PN 420	G 1 1/4 A		50	41	50	62	35.5	78.5	55	20	134.3	1 1 63 91 20 00	1 1 63 90 20 XX
S 38	PN 420	G 1 1/2 A		55	50	60	72	41	89	63	22	139.9	1 1 63 96 20 00	1 1 63 95 20 XX

Special pressure stages apply in  
combination with the 2S cutting  
ring (refer to Page 48)

Supplementary to Order No. for complete fitting tube connection	Supplementary to Order No.
2S	07
ES-4	09
BV-10	Refer to the front page

\* Apply to complete fittings with  
2S or ES-4 tube connection  
components.  
For BV-10 Refer to the front page.

\*\* With union nut and 2S, ES-4  
or BV-10 tube connection  
components

\*\*\* Sample product code, see:  
EL06LREDOMD