



# AG 5000

150


BMW B2 4006	FORD W-DX35-6203	PSA E24.54.815.G
MB B8 3180 220 000 001	GM 90.25	RENAULT EM24.54.700
VW 39D 878		NISSAN K32S0



ORDER	S (mm)	L1 ±0,25 (mm)	L (mm)	Kg.
AG 5000 012	12.7	165.4	152.7	9.90
AG 5000 025	25	190	165	10.40
AG 5000 038	38	216	178	10.92
AG 5000 050	50	240	190	11.41
AG 5000 063	63.5	267	203.5	11.96
AG 5000 080	80	300	220	12.63
AG 5000 100	100	340	240	13.45
AG 5000 125	125	390	265	14.47
AG 5000 160 *	160	460	300	15.89
AG 5000 200 *	200	540	340	17.52
AG 5000 250 *	250	640	390	19.55
AG 5000 300 *	300	740	440	21.59




CODE	Pressure (bar/psi)	F <sub>0</sub> (daN)	F <sub>1</sub> (daN)
AG 5000 050	150 / 2175	4980	7170
AG-H 5000 050	0 / 0	---	---



ENG ORDER  
 DEU BESTELLUNG  
 FRA COMMANDE  
 ITA ORDINE  
 ESP PEDIDO  
 POR PEDIDO

F<sub>0</sub> daN      S mm  
 AG 5000      50  
 AG 5000 050



N<sub>2</sub>      S<sub>max</sub> < 90%      V<sub>max</sub> 2 m/s      P<sub>min</sub> P<sub>max</sub> (20°C)      T<sub>min</sub> T<sub>max</sub>      600 CP-


N <sub>2</sub>	S <sub>max</sub> < 90%	V <sub>max</sub> 2 m/s	bar psi 20 290	bar psi 150 2175	°C °F 0 32	°C °F 80 176	600 CP-
----------------	------------------------	------------------------	----------------	------------------	------------	--------------	---------

# AG 5000 MOUNTS


**AZOL**  
**GAS**

ISO


## A14-120






## A34-120



## B21-120



## B76-120




CODE	AG 5000 050	KIT S-XXXXXXX KIT C-XXXXXXX	A14-120	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHEN	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GAS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA




# AG 5000 MOUNTS

ISO

## C05-120




## C20-120







## D02-120

2 x Ø13,5



## D67-120



CODE	AG 5000 050	KIT S-XXXXXXX KIT C-XXXXXXX	C05-120	18 CG 1-Q
ENG ORDER	GAS SPRING	REPAIR KIT	FLANGE	CHARGING ADAPTER
DEU BESTELLUNG	GASDRUCKFEDER	ERSATZTEILSATZ	FLANSCHSE	LADEADAPTER
FRA COMMANDE	RESSORT À GAZ	KIT DE RÉPARATION	BRIDE	RACCORD DE CHARGE
ITA ORDINE	CILINDRO AD AZOTO	KIT DI MANUTENZIONE	FLANGE	ADATTATORE DI CARICO
ESP PEDIDO	RESORTE DE GAS	KIT DE REPARACION	BRIDA	ADAPTADOR DE CARGA
POR PEDIDO	CILINDRO DE GÁS	KIT DE MANUTENÇÃO	FLANGE	ADAPTADOR DE CARGA