


**Śruba z łbem walcowym**

Socket head cap screw

**SM**



**Klasa** 12.9  
*Class*


d	D	s	k	t	l	R
M4	7	3	4	2	20	0,2
M5	8,5	4	5	2,5	22	
M6	10	5	6	3	24	0,25
M8	13	6	8	4	28	0,4
M10	16	8	10	5	32	
M12	18	10	12	6	38	0,6
M16	24	14	16	8	44	
M20	30	17	20	10	52	0,8
M24	36	19	24	12	60	

L	NR KAT.								
	d								
	M4	M5	M6	M8	M10	M12	M16	M20	M24
16			SM-06016	SM-08016	SM-10016				
20	SM-04020		SM-06020	SM-08020	SM-10020	SM-12020			
25			SM-06025	SM-08025	SM-10025	SM-12025	SM-16025		
30		SM-05030	SM-06030	SM-08030	SM-10030	SM-12030	SM-16030	SM-20030	
35			SM-06035	SM-08035	SM-10035	SM-12035	SM-16035		
40			SM-06040	SM-08040	SM-10040	SM-12040	SM-16040	SM-20040	SM-24040
45			SM-06045	SM-08045	SM-10045	SM-12045	SM-16045	SM-20045	
50			SM-06050	SM-08050	SM-10050	SM-12050	SM-16050	SM-20050	SM-24050
55			SM-06055	SM-08055	SM-10055	SM-12055	SM-16055	SM-20055	
60			SM-06060	SM-08060	SM-10060	SM-12060	SM-16060	SM-20060	SM-24060
65			SM-06065	SM-08065	SM-10065	SM-12065	SM-16065	SM-20065	
70			SM-06070	SM-08070	SM-10070	SM-12070	SM-16070	SM-20070	SM-24070
75			SM-06075	SM-08075	SM-10075	SM-12075	SM-16075		
80			SM-06080	SM-08080	SM-10080	SM-12080	SM-16080	SM-20080	SM-24080
90			SM-06090	SM-08090	SM-10090	SM-12090	SM-16090	SM-20090	SM-24090
100			SM-06100	SM-08100	SM-10100	SM-12100	SM-16100	SM-20100	SM-24100
110			SM-06110	SM-08110	SM-10110	SM-12110	SM-16110	SM-20110	SM-24110
120			SM-06120	SM-08120	SM-10120	SM-12120	SM-16120	SM-20120	SM-24120
130			SM-06130	SM-08130	SM-10130	SM-12130	SM-16130	SM-20130	SM-24130
140			SM-06140	SM-08140	SM-10140	SM-12140	SM-16140	SM-20140	SM-24140
150				SM-08150	SM-10150	SM-12150	SM-16150	SM-20150	SM-24150

# Śruba z łbem walcowym

Socket head cap screw

# SM



Klasa 12.9  
Class

d	D	s	k	t	l	R
M4	7	3	4	2	20	0,2
M5	8,5	4	5	2,5	22	
M6	10	5	6	3	24	0,25
M8	13	6	8	4	28	0,4
M10	16	8	10	5	32	
M12	18	10	12	6	38	0,6
M16	24	14	16	8	44	
M20	30	17	20	10	52	0,8
M24	36	19	24	12	60	

L	NR KAT.								
	d								
	M4	M5	M6	M8	M10	M12	M16	M20	M24
160			SM-06160	SM-08160	SM-10160	SM-12160	SM-16160	SM-20160	SM-24160
170						SM-12170	SM-16170	SM-20170	
180			SM-06180	SM-08180	SM-10180	SM-12180	SM-16180	SM-20180	SM-24180
190							SM-16190	SM-20190	
200			SM-06200	SM-08200	SM-10200	SM-12200	SM-16200	SM-20200	SM-24200
220				SM-08220	SM-10220	SM-12220	SM-16220	SM-20220	SM-24220
240					SM-10240	SM-12240	SM-16240	SM-20240	SM-24240
260					SM-10260	SM-12260	SM-16260	SM-20260	SM-24260
280					SM-10280	SM-12280	SM-16280	SM-20280	SM-24280
300							SM-16300	SM-20300	SM-24300
320								SM-20320	
340							SM-16340	SM-20340	SM-24340
360									
380							SM-16380		
400									
420							SM-16420		