


带轴配管型滚轮







①代号	类型	M材质	S表面处理
RRSN	直柱形	碳钢	无电解镀铬
RTSN	两端内螺纹型		
RDSN	两端挡圈槽型		

⚠️ 特点: 已完成轴的接合, 购入后即可使用。


按图定制



RRSN 直柱型






RTSN 两端内螺纹型



RDSN 两端挡圈槽型

其余^{6,7}

视角标准: 第一视角



①代号	-	②D	-	③d _{g6}	-	④L	-	⑤E	-	⑥F	-	⑦M	-	⑧N	-	⑨P	-	⑩S
RRSN	-	D50	-	d20	-	L200	-	E30	-	F30	-		-		-		-	
RTSN	-	D50	-	d20	-	L200	-	E30	-	F30	-	M12	-	N12	-		-	
RDSN	-	D50	-	d20	-	L200	-	E30	-	F30	-		-		-	P15	-	S35

型式	①代号	②D	③dg6	④L 指定单位10mm	⑤E-⑥F 指定单位1mm	⑦M(粗牙螺纹)-⑧N(细牙螺纹)	⑨P-⑩S 指定单位1mm	d _i	D _i	B	t	t公差	d _{zh7}	h7公差	适用挡圈
RRSN	50		15		5~45	5 6					1.15		14.3	⁰ _{-0.11}	C15
			20		5~60	5 6 8 10 12		40	43	25	1.35		19		C20
			25		5~75	5 6 8 10 12 16					1.35		23.9		C25
RTSN	60		20		5~60	5 6 8 10 12					1.35		19		C20
			25	100~500	5~75	5 6 8 10 12 16	5≤P<E-5 5≤S<F-5	49.5	53	30	1.35	+0.14 0	23.9	⁰ _{-0.21}	C25
			30		5~90	8 10 12 16 20					1.65		28.6		C30
RDSN	80		25		5~75	5 6 8 10 12 16					1.35		23.9		C25
			30		5~90	8 10 12 16 20		68.6	72	40	1.65		28.6		C30
			35		5~100	8 10 12 16 20 24					1.65		33	⁰ _{-0.25}	C35

E2
滚轮滚筒



爱安特自制模组, 火爆开售! 全零件备库, 最快 5 个工作日出货!

400-6699-428

www.ant-fa.com