


UITVOERING K / BAUFORM K / MOUNTING STYLE K



TYPE CILINDER				Afmetingen (mm)														
				R	L2	A	E	K	a2	b2	e1	f1	g1	h2	l	m2	x2	y1
ACDK- 40/	20 28	22 30	25	R3/8"	176	50	M16 x 1,5	41	50	25	30	20	19	24	48	67	12	16
ACDK- 50/	25	30	35	R3/8"	200	60	M16 x 1,5	46	55	28	35	25	23	29	57	75	15	16
ACDK- 60/	30	35	40	R1/2"	219	70	M22 x 1,5	53	65	33	40	30	28	30	61	82	16	22
ACDK- 63/	32 40	35 45	36	R1/2"	219	75	M22 x 1,5	56	65	33	40	30	28	30	61	82	16	22
ACDK- 65/	30 40	32 45	35	R1/2"	219	75	M22 x 1,5	56	65	33	40	30	28	30	61	82	16	22
ACDK- 70/	35 50	40	45	R1/2"	219	80	M22 x 1,5	58	65	33	40	30	28	30	61	82	16	22
ACDK- 80/	40 55	45 60	50	R1/2"	249	95	M28 x 1,5	66	83	41	50	35	30	35	68	93	17	28
ACDK- 90/	45 60	50 65	55	R1/2"	249	105	M28 x 1,5	71	83	41	50	35	30	35	68	93	17	28
ACDK-100/	50 70	55	60	R1/2"	267	115	M35 x 1,5	76	100	50	60	40	35	38	64	101	17	35
ACDK-110/	50 70	55	60	R1/2"	267	130	M35 x 1,5	84	100	50	60	40	35	38	64	101	17	35
ACDK-120/	60 85	70	80	R3/4"	320	140	M45 x 1,5	91	123	61	70	50	40	43	73	128	25	45
ACDK-125/	60 85	70 90	80	R3/4"	320	145	M45 x 1,5	94	123	61	70	50	40	43	73	128	25	45
ACDK-130/	70	80	85	R3/4"	320	150	M58 x 1,5	96	140	70	70	60	50	54	73	128	25	58
ACDK-140/	70 90	80 100	85	R3/4"	392	160	M65 x 1,5	101	164	82	75	70	55	65	108	147	35	65
ACDK-150/	80 100	85	90	R3/4"	392	170	M65 x 1,5	106	164	82	75	70	55	65	108	147	35	65
ACDK-160/	85 110	90	100	R1"	477	180	M80 x 2	115	180	90	95	80	60	74	140	177	37	80