




①代号	④材质	⑤表面处理/颜色
PHTPBA	PF	黑色
PHTPBB		红色
PHTNBA	PA6+GF30	黑色



视角标准：第一视角



①代号 - ②L
PHTPBA - L90

①代号	型号	M	a	b	h	H		L ₁	参考重量 (kg/pcs)
						PHTPBA	PHTPBB		
PHTPBA PHTPBB	90	M6	24	16	12	45	45	106	0.07
	*90A		32	21	22	50	-	110	0.09
	*114		27.5	20	16	50	50	132	0.10
	120		32	21	22	60	-	162	0.15
	*120A		27.5	20	16	50	50	176	0.16
	*140	M8	27.5	20	16	55	55	196	0.19
	160		32	21	22	60	-	182	0.17
	*160A		27.5	20	16	55	55	202	0.20
	180		32	21	22	60	-	222	0.21
	*180A	M8	27.5	20	16	60	60	256	0.22
	*200		32	21	22	65	65	336	0.30
	240		27.5	20	16	65	65	416	0.37
	320		27.5	20	16	65	65	416	0.37
	400								

▲带*仅适用于PHTPBA

①代号	型号	M	a	b	h	H	L ₁	参考重量 (kg/pcs)
PHTNBA	90	M6	28	18	14	50	108	0.01
	117		25	16	12	48	134	
	120	M8					140	0.02
	180		28	20	16	60	200	
	240						260	



数量分类	小单	中大单	大单
数量	1~50	51~100	100~
交货期	通常	7工作日	现询



数量	1~9	10~
价格	100%	现询

G1
合页/门组件
手柄/手柄拉手

