

金属垫圈 淬火型



★ 产品特点: 切削加工制作的高精度产品, 可实现高精度空间调整。

类型		M材质	S表面处理	A硬度
普通级	精密级			
MWCAC	MWCCC	一般结构用钢	四氧化三铁保护膜 无电镀镍	45-50HRC
MWDAC	MWDCC			

⚠ 如对防锈有要求, 请优先选用不锈钢材质或无电镀镍产品。

3 Q^{+0.3}/_{+0.1}
2 D⁰/_{-0.2}

D ≤ 16 C < 0.2
D ≥ 20 C < 0.5
D ≤ 16 C < 0.2
D ≥ 20 C < 0.5
6.3
4 B ± 0.1

普通级

D ≤ 16 C < 0.2
D ≥ 20 C < 0.5
D ≤ 16 C < 0.2
D ≥ 20 C < 0.5
1.6
1.6
4 B ± 0.01

精密级

视角标准: 第一视角



①代号 - ②D - ③Q - ④B
MWCAC - D4 - Q2 - B1

①代号	②D		③Q								④B											
(普通级) MWCAC MWDAC	4	2									1	2										
	5	2	3								1	2										
	6	2	3	4							1	2										
	8	2	3	4	5	6				1	2	3	5									
	10	2	3	4	5	6	8				1	2	3	5								
	12		3	4	5	6	8	10				1	2	3	5							
	13			4	5	6	8	10				1	2	3	5							
	14			4	5	6	8	10				1	2	3	5							
	15			4	5	6	8	10	12				1	2	3	5						
	(精密级) MWCCC MWDCC	16		4	5	6	8	10	12				1	2	3	5						
20				4	5	6	8	10	12	15	16				2	3	5					
25					6	8	10	12	15	16	20				2	3	5					
30						8	10	12	15	16	20	25				2	3	5				
35							10	12	15	16	20	25					3	5	10			
40								10	12	15	16	20	25	30					3	5	10	
50									10	12	15	16	20	25	30					3	5	10
60											15	16	20	25	30					3	5	10



交货期

1天发货

数量分类	标准订单	特殊订单
	小单	大单
数量	1-200	201~
交货期	1天发货	另行报价

⚠ 常州工厂发货。

⚠ 部分产品型号 7 天发货, 请以报价为准。

A6
垫圈、轴环

