

## Anaconda stainless steel AISI-316 fittings for Anaconda Sealrite.

The stainless steel AISI-316 Anaconda fittings can be used with all types of Anaconda Sealrite (except CNP) and offer the highest corrosion resistance. These stainless steel Anaconda fittings are mostly used in the off-shore, chemical and food industry. Because of the UL & CSA approvals the fittings are also suitable for export projects outside Europe.

### Material & Construction:

**Construction:** Stainless steel (AISI-316) fitting, consisting of 4 parts (counter nut, clamping ring, ferrule and body).

**Material:** Counter nut and body are stainless steel (AISI-

316) and the ferrule is from nickel plated brass. Clamping ring and insert are from PA6 (red for ISO metric and white for NPT).

**Special approvals:** UL-514B and CSA C 22.2 (combined UL/CSA file # E 234207).


Suitable for use in hazardous environments according NEC 501-4B Class I, Division 2; Class II, Division 1 and 2; Class III, Division 1 and 2.

**Temperature:** -45 °C till +105 °C continuous.

**Protection class:** IP 67 (dust-proof, water-tight).


**Colour:** Metal.

### ISO straight fitting, male, stainless steel (AISI-316).



Thread	Sealrite Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
M16 x 1,5	3/8"	10,2	35	12	26	-	24	10	812.116.9	5,2
M20 x 1,5	1/2"	13,9	37	13	29	-	27	10	812.120.9	6,4
M25 x 1,5	3/4"	18,5	40	15	35	-	33	5	812.125.9	8,5
M32 x 1,5	1"	23,8	46	15	45	-	43	5	812.132.9	18,5

### Pg straight fitting, male, stainless steel (AISI-316).



Thread	Sealrite Size (inch)	Min. Internal Bore (mm)	Dimensions in mm					Standard Package	Article Number	Weight (Kg/100)
			A	B	C	D	E			
Pg 16	1/2"	13,9	37	13	30	-	27	10	810.116.9	6,8
Pg 21	3/4"	18,5	40	15	36	-	36	5	810.121.9	9,1
Pg 29	1"	23,8	46	15	46	-	46	5	810.129.9	27,0

ANACONDA  
SEALRITE®  
SPECIAL

LIQUID-TIGHT  
FITTINGS FOR  
SEALRITE  
IP 67