

SERIES 72GS

SILICON RUBBER WHEELS FOR HIGH TEMPERATURES AND ALUMINIUM CENTRE



Wheel description

Red non-staining silicone rubber wheels, hardness 80+/-5 Shore A, aluminium centre.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z.

Diameters: 100 mm

Carrying capacity: 80 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

Uses

Environments

It is suitable for use in indoor environments and resistant to most of the chemical agents used in the food industry; is particularly recommended in bread baking ovens. It has excellent elasticity and is guaranteed to easily overcome obstacles on uneven surfaces.

Usage temperatures: from -30°C to +250°C; for used at temperatures higher than 130 °C, wheel load capacity should be reduced by 50%.

Floors



Handling

