


The Standard - Option KMA* - pivoting

- Recommended for unsupported and gliding applications
- Confined installation conditions
- Option - integrated C-profile strain relief device with Chainfix clip or strain relief tiwrap plates
- Corrosion resistant
- Universal mountable with attachment capability on all sides

*KMA = Polymer Metal Mounting Bracket


Moving end

3800/7800...□.2





Fixed end

3800/7800...□.1



The attachment variants arising automatically by the choice of the KMA mounting bracket



Option KMA - locking


- Recommended for vertical hanging / standing applications

Additionally:

- Universal mountable
- C-profile option
- Corrosion resistant
- Locked connections
- At very high acceleration

Moving end

3900/7900...□.2




Fixed end

3900/7900...□.1



The attachment variants arising automatically by the choice of the KMA mounting bracket



Fixed end


3800/7800...□.1 (pivoting)

3900/7900...□.1 (locking)

Moving end

(pivoting) 3800/7800...□.2

(locking) 3900/7900...□.2




Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]	Width index	Part No. full set pivoting	Part No. full set locking	C-profile option [mm]
.05.	3800/7800	3900/7900	.05. □.12. C 50	.23.	3800	3900	.23. □.12. C 225
.06.	3800	3900	.06. □.12. C 68	.237	3800	3900	.237. □.12. C 237
.07.	3800/7800	3900/7900	.07. □.12. C 75	.25.	3800/7800	3900/7900	.25. □.12. C 250
.087.	3800	3900	.087. □.12. C 87	.262	3800	3900	.262. □.12. C 262
.10.	3800/7800	3900/7900	.10. □.12. C 100	.28.	3800	3900	.28. □.12. C 275
.11.	3800/7800	3900/7900	.11. □.12. C 108	.29.	3800	3900	.29. □.12. C 287
.112.	3800	3900	.112. □.12. C 112	.30.	3800/7800	3900/7900	.30. □.12. C 300
.12.	3800/7800	3900/7900	.12. □.12. C 125	.312.	3800	3900	.312. □.12. C 312
.137.	3800	3900	.137. □.12. C 137	.325.	3800	3900	.325. □.12. C 325
.15.	3800/7800	3900/7900	.15. □.12. C 150	.337.	3800	3900	.337. □.12. C 337
.162.	3800	3900	.162. □.12. C 162	.350.	3800	3900	.350. □.12. C 350
.17.	3800/7800	3900/7900	.17. □.12. C 168	.362.	3800	3900	.362. □.12. C 362
.18.	3800	3900	.18. □.12. C 175	.375.	3800	3900	.375. □.12. C 375
.187.	3800	3900	.187. □.12. C 187	.387.	3800	3900	.387. □.12. C 387
.20.	3800/7800	3900/7900	.20. □.12. C 200	.400.	3800	3900	.400. □.12. C 400
.212.	3800	3900	.212. □.12. C 212				


Please insert 1 for odd number of links or 2 for even number of links

Dimensions and order configurations

Part No. structure (pivoting)



Part No. structure (locking)



Note: The E4/00 System may end with either an inner side or an outer side link. Keep in mind that an outer side link always forms the first chain link at the moving end. The Part No. depends on an even or odd numbers of links. Please insert: 1 for odd number of links or 2 for even number of links

Full set, for both ends:

3800.05.2.12.C (even)

Single-part order:

3800.05.2.2.C (even)

Mounting bracket moving end

3800.05.2.1.C (even)

Mounting bracket fixed end

