



Part No. structure

T3.29.100.038.0



Series T3.29 - with crossbars every 2nd link

Part No.	B_i [mm]	B_a [mm]	R [mm]	Bending radii	Weight [kg/m]
T3.29.030.□.0	30	55	038		≈ 0,40
T3.29.040.□.0	40	65	038		≈ 0,42
T3.29.050.□.0	50	75	038		≈ 0,44
T3.29.060.□.0	60	85	038		≈ 0,46
T3.29.070.□.0	70	95	038		≈ 0,48
T3.29.080.□.0	80	105	038		≈ 0,50
T3.29.090.□.0	90	115	038		≈ 0,51
T3.29.100.□.0	100	125	038		≈ 0,53
T3.29.110.□.0	110	135	038		≈ 0,55
T3.29.120.□.0	120	145	038		≈ 0,57

Supplement Part No. with required radius. Example: T3.29.100.038.0

0 = standard color, other colors ► page 1.39 · Pitch = 15 mm/link - Links/m = 67



Interior separation elements

Distance "Z" for the interior separation elements of the T3 E-Chain®

Note: The first and last chain links should not be stuck with the interior separation elements!

As a standard, crossbars are mounted on every 4th chain link!

Part No. T3.29.100.038.0

For other distances, e.g. every 6th chain link, change the part number as follows:

Part No. T3.29.100.038.Z6.0

